


BGA Adapters



Features:

- Soldering BGA Device to adapter subjects BGA to less thermal stress than soldering BGA directly to a PCB due to the adapter's lower mass.
- Uses same footprint as BGA device.
- Custom adapters available for heat sink attachment.
- Gold plated screw-machined terminals for superior durability.
- Unique SMT Adapter provides reliable solution for mounting or socketing LGA or re-worked BGA devices.
- SMT Adapters mate with our BGA Sockets for LGA to BGA conversion or SMT Board to Board applications.

Specifications:

Terminals:

Brass - Copper Alloy
(C36000) ASTM-B-16

Solder Ball:

Standard: 63Sn/37Pb
Lead-free: 95.5Sn/4.0Ag/0.5Cu

Plating:

G - Gold over Nickel

Gold per ASTM-B-488
Nickel per QQ-N-290



5 Energy Way, West Warwick, RI 02893 USA
Tel: 800.424.9850 | 401.823.5200
Fax: 401.823.8723
info@advanced.com | www.advanced.com
Catalog 16 rev. Sept. 07

Ball Grid Array (BGA) Adapters For use with BGA Sockets on pages 8-9

Table of Models

	Description: Standard Adapter (A) Material: FR-4 Fiberglass Epoxy Board Index: -40°C to 140°C (-40°F to 284°F) Note: Mates with Standard Socket (S)	Insulator Size: BGA device body +.079/(2.00mm)
	Description: Extraction Slot Adapter (AX) Material: FR-4 Fiberglass Epoxy Board Index: -40°C to 140°C (-40°F to 284°F) Note: Mates with Extraction Socket (SB)	Insulator Size: BGA device body +.157/(4.00mm)

Note: For use with LGA or reworked BGA devices, select surface mount (SMT) terminals which feature solder balls on device side. SMT Adapter terminals may also be used for surface mount board to board applications.


Options




P/N 8125

Extraction Tool

- Insert "T" bar end of tool into extraction slot adapter.
- Slide tool to end of slot and pry adapter from socket.
- Repeat in additional slots until adapter is separated from socket.
- Works with LCP or FR-4 sockets.



How To Order



Note: See pages 4-5 for 0.50mm and 0.65mm pitch.
Consult factory for custom 0.75mm pitch designs.
For SMT Adapters, select Model Type A or AX
and appropriate SMT Terminal Type from page 7.

Ball Grid Array (BGA) Adapters


For use with BGA Sockets on pages 8-9

Additional standard and custom terminals available.
See Terminals section or consult factory.

Standard Terminals


Standard

Type -638 1.27mm pitch	Type -715 1.00mm pitch	Type -700 0.80mm pitch




Male to Male

Type -721 1.27mm pitch	Type -735 1.00mm pitch	Type -732 0.80mm pitch




SMT (Surface Mount)

Tin/Lead: Type -720 Lead-free: Type -823 1.27mm pitch	Tin/Lead: Type -737 Lead-free: Type -824 1.00mm pitch	Tin/Lead: Type -736 Lead-free: Type -829 0.80mm pitch




How It Works

See page 15 for Generic Reflow Profiles.



- Either Tin/Lead or Lead-free device packages can be attached to our RoHS Compliant Adapters.
- PC boards can be processed with Tin/Lead BGA sockets in standard profiles or lead-free BGA sockets in RoHS Compliant, high temperature profiles.

Dimensional Information




Standard Adapter (A)

- Mates with Standard Socket (S)
- Adapter size equals BGA Device body + .079/(2.00)

Extraction Slot Adapter (AX)


- Slots allow AIC extraction tool (sold separately) to easily remove device/adapter assembly from socket
- Mates with Extraction Socket (SB)
- Adapter size equals BGA Device body + .157/(4.00)

BGA Adapters



Footprints:

360 Pins
Footprint Number 360-2



22 x 22 rows

- Footprint specific insulators drilled to exact device pattern.
- Over 1000 footprints available - see page 88, search online or submit your device specs.
- Use our Build-A-Part feature or search in our online BGA Socket Finder™ at www.bgasockets.com.

Available Online:

- RoHS Qualification Test Report
- Technical articles
- Test data
- Signal Integrity Performance
- CAD Drawings
- BGA Footprints




5 Energy Way, West Warwick, RI 02893 USA
Tel: 800.424.9850 | 401.823.5200
Fax: 401.823.8723
info@advanced.com | www.advanced.com
Catalog 16 rev. Sept. 07

inch/(mm)

Products shown covered by patents issued and/or pending. Specifications subject to change without notice.

BGA Adapter Sockets



Features:

- Advanced® exclusive solder ball terminals offer superior SMT processing.
- Same footprint as BGA device.
- Proven long-term performance in vigorous temperature cycling applications - solder ball terminal absorbs TCE mismatch.
- Closed bottom socket terminal for 100% anti-wicking of solder.
- Gold contacts allow gold/gold interconnections to Adapter pins.
- Low insertion force socket with multi-fingered high reliability Beryllium Copper contacts.
- Coplanarity consistently under .006 inch industry standard.
- Custom designs available.

Specifications:

Terminals:

Brass - Copper Alloy
(C36000) ASTM-B-16

Contacts:

Beryllium Copper
(C17200) ASTM-B-194

Solder Ball:

Standard: 63Sn/37Pb
Lead-free: 95.5Sn/4.0Ag/0.5Cu



Plating:

G - Gold over Nickel
Gold per ASTM-B-488
Nickel per QQ-N-290

Ball Grid Array (BGA) Adapter Sockets

For use with BGA Adapters on pages 6-7

Table of Models

	Description: Standard Socket (S) Mat'l: High Temp. Liquid Crystal Polymer (LCP)* Index: -60°C to 260°C (-76°F to 500°F)	Insulator Size: Same size as BGA device body
	Description: Extraction Socket (SB) Mat'l: High Temp. Liquid Crystal Polymer (LCP)* Index: -60°C to 260°C (-76°F to 500°F)	Insulator Size: 1.27mm Pitch: BGA device body +.079/(2.00) 1.00mm Pitch: BGA device body +.138/(3.50)

RGS/RGSB replaces MGS/MGSB, MHS/MHSB replaces FHS/FHSB.

* Some sizes may only be available in FR-4. See How To Order section or consult factory.

Options




Tape and Reel Packaging

- Conforms to EIA-481 Standard.
- Pick-up tape included.
- Add -TR to end of part number when ordering.
- Custom packaging available
- If -TR is not specified, standard tray packs are used.



- Extraction tool (P/N 8125) is available separately.
- Works with Extraction Slot Adapters and LCP or FR-4 sockets.

How To Order



Note: See pages 4-5 for 0.50mm and 0.65mm pitch.



5 Energy Way, West Warwick, RI 02893 USA
Tel: 800.424.9850 | 401.823.5200
Fax: 401.823.8723
info@advanced.com | www.advanced.com
Catalog 16 rev. Sept. 07

Products shown covered by patents issued and/or pending. Specifications subject to change without notice.

inch/(mm)

Ball Grid Array (BGA) Adapter Sockets

For use with BGA Adapters on pages 6-7

Additional standard and custom terminals available.
See Terminals section or consult factory.

Standard Terminals

SMT (Surface Mount)


Tin/Lead: Type -636 Lead-free: Type -819 1.27mm pitch PATENTED	Tin/Lead: Type -790 Lead-free: Type -788 1.00mm pitch PATENTED	Tin/Lead: Type -702 Lead-free: Type -828 0.80mm pitch PATENTED
---	---	---

Thru-Hole

Type -673 1.27mm pitch PATENTED	Type -789 1.00mm pitch PATENTED	Type -731 0.80mm pitch PATENTED
--	--	--


How It Works

See page 15 for Generic Reflow Profiles.




- Either Tin/Lead or Lead-free device packages can be attached to our RoHS Compliant Adapters.
- PC boards can be processed with Tin/Lead BGA sockets in standard profiles or lead-free BGA sockets in RoHS Compliant, high temperature profiles.

Dimensional Information



Standard Socket (S)


- Mates with Standard Adapter (A)
- Socket size same as BGA device body
- Use with SMT Adapter for LGA and reworked BGA device socketing (or board to board applications)



Extraction Socket (SB)


- Mates with Extraction Slot Adapter (AX)
- Socket size equals BGA body + .079/(2.00) for 1.27mm pitch or BGA body + .138/(3.50) for 1.00mm pitch
- Protects valuable PCB during device/adapter extraction - tool never touches PCB
- Available in 1.00 and 1.27mm pitch only

BGA Adapter Sockets



Footprints:

360 Pins
Footprint Number 360-2



22 x 22 rows

- Full grid molded insulators populated to exact device pattern.
- Over 1000 footprints available - see page 88, search online or submit your device specs.
- Use our Build-A-Part feature or search in our online BGA Socket Finder™ at www.bgasockets.com.

Available Online:

- RoHS Qualification Test Report
- Technical articles
- Test data
- Signal Integrity Performance
- CAD drawings
- Generic Tin/Lead and Lead-free Reflow Profiles



5 Energy Way, West Warwick, RI 02893 USA
Tel: 800.424.9850 | 401.823.5200
Fax: 401.823.8723
info@advanced.com | www.advanced.com
Catalog 16 rev. Sept. 07

inch/(mm)

Products shown covered by patents issued and/or pending. Specifications subject to change without notice.